

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247204

Luminaire Tested: P3AS17R209024DE010 E3D1B

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209024DE010 E3D1B
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3D1B TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1424.0 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247204
CATALOG NUMBER: P3AS17R209024DE010 E3D1B

Luminous Intensity Polar Plot





TEST NUMBER: P1247204
 CATALOG NUMBER: P3AS17R209024DE010 E3D1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2160090
5°	1818705
10°	1135940
15°	424679
20°	145776
25°	60754
30°	28612
35°	12822
40°	6069
45°	3101
50°	1126
55°	229
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3101 cd/sqm



TEST NUMBER: P1247204
 CATALOG NUMBER: P3AS17R209024DE010 E3D1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	687.1	48.2
10°-20°	566.0	39.7
20°-30°	128.6	9.0
30°-40°	32.7	2.3
40°-50°	8.2	0.6
50°-60°	1.1	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.6	97.0
0°-40°	1414.4	99.3
0°-60°	1423.7	100.0
0°-90°	1424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9851	
5°	8262	687
15°	1871	566
25°	251	129
35°	48	33
45°	10	8
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1247204
CATALOG NUMBER: P3AS17R209024DE010 E3D1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	9850.8
1°	9767.3
2°	9521.2
3°	9168.2
4°	8735.1
5°	8262.4
6°	7735.7
7°	7154.4
8°	6476.3
9°	5804.3
10°	5101.6
11°	4353.9
12°	3607.3
13°	2974.8
14°	2370.1
15°	1870.7
16°	1476.5
17°	1164.7
18°	935.9
19°	761.1
20°	624.7
21°	522.2
22°	435.9
23°	362.5
24°	302.3
25°	251.1
27.5°	164.2
30°	113.0
32.5°	69.6
35°	47.9
37.5°	30.6
40°	21.2
42.5°	14.5
45°	10.0
47.5°	6.7
50°	3.3
52.5°	1.7
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1247204
CATALOG NUMBER: P3AS17R209024DE010 E3D1B

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)