

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248796

Luminaire Tested: P3AS09R209027DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209027DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 538.0 lumens
Efficiency: N/A
Efficacy: 48.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248796

CATALOG NUMBER: P3AS09R209027DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1248796

CATALOG NUMBER: P3AS09R209027DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133081
5°	129518
10°	119147
15°	104881
20°	89934
25°	75561
30°	61073
35°	46471
40°	33062
45°	21832
50°	13509
55°	8869
60°	8113
65°	7472
70°	6988
75°	6354
80°	6061
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21832 cd/sqm

TEST NUMBER: P1248796

CATALOG NUMBER: P3AS09R209027DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	10.1
10°-20°	128.6	23.9
20°-30°	142.8	26.5
30°-40°	108.9	20.2
40°-50°	55.8	10.4
50°-60°	22.9	4.3
60°-70°	14.3	2.7
70°-80°	8.0	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.8	60.6
0°-40°	434.7	80.8
0°-60°	513.4	95.4
0°-90°	538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	607	
5°	588	54
15°	462	129
25°	312	143
35°	174	109
45°	70	56
55°	23	23
65°	14	14
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1248796

CATALOG NUMBER: P3AS09R209027DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	606.9
1°	607.6
2°	604.8
3°	601.4
4°	595.9
5°	588.4
6°	579.5
7°	570.0
8°	559.7
9°	547.4
10°	535.1
12.5°	499.6
15°	462.0
17.5°	423.7
20°	385.4
22.5°	347.2
25°	312.3
27.5°	277.5
30°	241.2
32.5°	207.1
35°	173.6
37.5°	144.2
40°	115.5
42.5°	90.9
45°	70.4
47.5°	53.3
50°	39.6
52.5°	29.4
55°	23.2
57.5°	21.2
60°	18.5
62.5°	16.4
65°	14.4
67.5°	12.3
70°	10.9
72.5°	8.9
75°	7.5
77.5°	6.2
80°	4.8
82.5°	3.4
85°	2.1
87.5°	0.7
90°	0.0

(END OF REPORT)