

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247231

Luminaire Tested: P3AS17R259024DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259024DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1535.1 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247231

CATALOG NUMBER: P3AS17R259024DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1247231

CATALOG NUMBER: P3AS17R259024DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	96	96
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	93	93
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	88	88
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	86	86
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	84	84
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	82	82
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	80	80
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	78	78
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1681115
5°	1557315
10°	1204899
15°	575508
20°	189740
25°	79988
30°	30992
35°	13411
40°	4466
45°	2078
50°	751
55°	421
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2078 cd/sqm

TEST NUMBER: P1247231

CATALOG NUMBER: P3AS17R259024DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	621.9	40.5
10°-20°	707.3	46.1
20°-30°	164.4	10.7
30°-40°	34.5	2.2
40°-50°	5.6	0.4
50°-60°	0.9	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1493.5	97.3
0°-40°	1528.0	99.5
0°-60°	1534.5	100.0
0°-90°	1535.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1535.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7666	
5°	7075	622
15°	2535	707
25°	331	164
35°	50	34
45°	7	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247231

CATALOG NUMBER: P3AS17R259024DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7666.5
1°	7650.9
2°	7571.3
3°	7459.4
4°	7288.6
5°	7074.9
6°	6800.5
7°	6513.3
8°	6191.1
9°	5827.6
10°	5411.3
11°	4928.8
12°	4375.0
13°	3768.4
14°	3133.9
15°	2535.1
16°	2005.3
17°	1562.2
18°	1228.9
19°	982.9
20°	813.1
21°	679.5
22°	570.5
23°	476.4
24°	398.5
25°	330.6
27.5°	195.9
30°	122.4
32.5°	78.5
35°	50.1
37.5°	30.1
40°	15.6
42.5°	10.0
45°	6.7
47.5°	3.9
50°	2.2
52.5°	1.1
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0



TEST NUMBER: P1247231

CATALOG NUMBER: P3AS17R259024DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)