

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248818

Luminaire Tested: P3AS09R259027DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259027DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 438.0 lumens
Efficiency: N/A
Efficacy: 39.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248818

CATALOG NUMBER: P3AS09R259027DE010 E3DL1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1248818

CATALOG NUMBER: P3AS09R259027DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159022
5°	152564
10°	133643
15°	107424
20°	82537
25°	62447
30°	45121
35°	29982
40°	18177
45°	10575
50°	6755
55°	5467
60°	4780
65°	4255
70°	3526
75°	3474
80°	2526
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10575 cd/sqm

TEST NUMBER: P1248818

CATALOG NUMBER: P3AS09R259027DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	14.4
10°-20°	130.9	29.9
20°-30°	118.3	27.0
30°-40°	71.1	16.2
40°-50°	28.2	6.4
50°-60°	13.0	3.0
60°-70°	7.9	1.8
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.3	71.3
0°-40°	383.4	87.5
0°-60°	424.6	96.9
0°-90°	438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	725	
5°	693	63
15°	473	131
25°	258	118
35°	112	71
45°	34	28
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1248818

CATALOG NUMBER: P3AS09R259027DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	725.2
1°	725.2
2°	721.8
3°	714.3
4°	704.7
5°	693.1
6°	678.1
7°	661.0
8°	641.2
9°	621.4
10°	600.2
11°	575.6
12°	550.4
13°	525.1
14°	499.8
15°	473.2
17.5°	410.4
20°	353.7
22.5°	302.5
25°	258.1
27.5°	216.5
30°	178.2
32.5°	143.4
35°	112.0
37.5°	85.4
40°	63.5
42.5°	46.4
45°	34.1
47.5°	25.9
50°	19.8
52.5°	16.4
55°	14.3
57.5°	12.3
60°	10.9
62.5°	8.9
65°	8.2
67.5°	6.8
70°	5.5
72.5°	4.8
75°	4.1
77.5°	3.4
80°	2.0
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1248818

CATALOG NUMBER: P3AS09R259027DE010 E3DL1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)