

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247294

Luminaire Tested: P3AS17R359024DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247294  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359024DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1442.0 lumens  
Efficiency: N/A  
Efficacy: 68.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247294  
CATALOG NUMBER: P3AS17R359024DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1247294  
 CATALOG NUMBER: P3AS17R359024DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89			89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83			83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80			80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78			78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75			75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73			73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70			70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	940276
5°	921129
10°	856920
15°	628267
20°	321701
25°	115942
30°	45146
35°	15821
40°	6498
45°	1768
50°	1535
55°	1720
60°	1491
65°	1193
70°	1475
75°	1949
80°	1389
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 1949 cd/sqm



TEST NUMBER: P1247294  
 CATALOG NUMBER: P3AS17R359024DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	390.1	27.1
10°-20°	732.0	50.8
20°-30°	259.2	18.0
30°-40°	45.4	3.1
40°-50°	6.6	0.5
50°-60°	3.7	0.3
60°-70°	2.7	0.2
70°-80°	2.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.2	95.8
0°-40°	1426.6	98.9
0°-60°	1436.9	99.6
0°-90°	1442.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1442.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4288	
5°	4185	390
15°	2768	732
25°	479	259
35°	59	45
45°	6	7
55°	4	4
65°	2	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1247294  
CATALOG NUMBER: P3AS17R359024DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4288.0
1°	4286.9
2°	4273.3
3°	4247.1
4°	4223.3
5°	4184.7
6°	4144.9
7°	4100.6
8°	4046.1
9°	3961.0
10°	3848.5
11°	3693.0
12°	3505.6
13°	3283.0
14°	3037.7
15°	2767.5
17.5°	2061.1
20°	1378.6
22.5°	831.3
25°	479.2
27.5°	286.2
30°	178.3
32.5°	103.3
35°	59.1
37.5°	37.5
40°	22.7
42.5°	11.4
45°	5.7
47.5°	4.5
50°	4.5
52.5°	4.5
55°	4.5
57.5°	3.4
60°	3.4
62.5°	3.4
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0



TEST NUMBER: P1247294  
CATALOG NUMBER: P3AS17R359024DE010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)