

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248871

Luminaire Tested: P3AS09R359027DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359027DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 868.1 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248871

CATALOG NUMBER: P3AS09R359027DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1248871

CATALOG NUMBER: P3AS09R359027DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	565985
5°	554456
10°	515822
15°	378163
20°	193637
25°	69802
30°	27169
35°	9503
40°	3922
45°	1054
50°	921
55°	1032
60°	921
65°	726
70°	898
75°	1186
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 1186 cd/sqm

TEST NUMBER: P1248871

CATALOG NUMBER: P3AS09R359027DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.8	27.1
10°-20°	440.6	50.8
20°-30°	156.0	18.0
30°-40°	27.3	3.1
40°-50°	4.0	0.5
50°-60°	2.2	0.3
60°-70°	1.6	0.2
70°-80°	1.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.4	95.8
0°-40°	858.7	98.9
0°-60°	864.9	99.6
0°-90°	868.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	868.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2581	
5°	2519	235
15°	1666	441
25°	288	156
35°	36	27
45°	3	4
55°	3	2
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248871

CATALOG NUMBER: P3AS09R359027DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2581.1
1°	2580.5
2°	2572.3
3°	2556.5
4°	2542.2
5°	2518.9
6°	2495.0
7°	2468.3
8°	2435.5
9°	2384.3
10°	2316.6
11°	2222.9
12°	2110.2
13°	1976.2
14°	1828.5
15°	1665.8
17.5°	1240.7
20°	829.8
22.5°	500.4
25°	288.5
27.5°	172.3
30°	107.3
32.5°	62.2
35°	35.5
37.5°	22.6
40°	13.7
42.5°	6.8
45°	3.4
47.5°	2.7
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.1
60°	2.1
62.5°	2.1
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1248871

CATALOG NUMBER: P3AS09R359027DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)