

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247334

Luminaire Tested: P3AS17R409024DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247334  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R409024DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1015.0 lumens  
Efficiency: N/A  
Efficacy: 47.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247334  
CATALOG NUMBER: P3AS17R409024DE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1247334  
 CATALOG NUMBER: P3AS17R409024DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	227855
5°	223728
10°	210885
15°	191533
20°	168271
25°	143694
30°	119031
35°	91792
40°	65351
45°	44005
50°	24016
55°	16936
60°	15920
65°	14736
70°	13079
75°	12539
80°	9976
85°	8554

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 44005 cd/sqm



TEST NUMBER: P1247334  
 CATALOG NUMBER: P3AS17R409024DE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.8	9.3
10°-20°	235.0	23.2
20°-30°	271.7	26.8
30°-40°	214.1	21.1
40°-50°	109.9	10.8
50°-60°	42.0	4.1
60°-70°	27.8	2.7
70°-80°	15.1	1.5
80°-90°	4.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.5	59.3
0°-40°	815.7	80.4
0°-60°	967.6	95.3
0°-90°	1015.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1015.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1039	
5°	1016	95
15°	844	235
25°	594	272
35°	343	214
45°	142	110
55°	44	42
65°	28	28
75°	15	15
85°	3	4
90°	0	



TEST NUMBER: P1247334  
CATALOG NUMBER: P3AS17R409024DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1039.1
2.5°	1033.4
5°	1016.4
7.5°	986.8
10°	947.1
12.5°	900.5
15°	843.7
17.5°	784.7
20°	721.1
22.5°	656.4
25°	593.9
27.5°	531.5
30°	470.1
32.5°	407.7
35°	342.9
37.5°	282.8
40°	228.3
42.5°	181.7
45°	141.9
47.5°	103.3
50°	70.4
52.5°	51.1
55°	44.3
57.5°	39.7
60°	36.3
62.5°	31.8
65°	28.4
67.5°	23.8
70°	20.4
72.5°	17.0
75°	14.8
77.5°	11.4
80°	7.9
82.5°	6.8
85°	3.4
87.5°	2.3
90°	0.0

(END OF REPORT)