

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247368

Luminaire Tested: P3AS17R459024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1270.0 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247368

CATALOG NUMBER: P3AS17R459024DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1247368

CATALOG NUMBER: P3AS17R459024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	476935
5°	465748
10°	428137
15°	362772
20°	281471
25°	196753
30°	123943
35°	72973
40°	41277
45°	20064
50°	6959
55°	5658
60°	5482
65°	5292
70°	5129
75°	4829
80°	4293
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20064 cd/sqm

TEST NUMBER: P1247368

CATALOG NUMBER: P3AS17R459024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.9	15.4
10°-20°	438.8	34.6
20°-30°	372.6	29.3
30°-40°	177.8	14.0
40°-50°	53.5	4.2
50°-60°	13.6	1.1
60°-70°	10.1	0.8
70°-80°	6.0	0.5
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1007.3	79.3
0°-40°	1185.1	93.3
0°-60°	1252.2	98.6
0°-90°	1270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1270.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2175	
5°	2116	196
15°	1598	439
25°	813	373
35°	273	178
45°	65	54
55°	15	14
65°	10	10
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1247368

CATALOG NUMBER: P3AS17R459024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2175.0
2.5°	2161.3
5°	2115.9
7.5°	2037.5
10°	1922.8
12.5°	1770.6
15°	1598.0
17.5°	1406.1
20°	1206.2
22.5°	1002.9
25°	813.2
27.5°	640.6
30°	489.5
32.5°	368.0
35°	272.6
37.5°	201.0
40°	144.2
42.5°	99.9
45°	64.7
47.5°	36.3
50°	20.4
52.5°	15.9
55°	14.8
57.5°	13.6
60°	12.5
62.5°	11.4
65°	10.2
67.5°	9.1
70°	8.0
72.5°	6.8
75°	5.7
77.5°	4.5
80°	3.4
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)