

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248891

Luminaire Tested: P3AS09R359027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 443.0 lumens
Efficiency: N/A
Efficacy: 39.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248891

CATALOG NUMBER: P3AS09R359027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248891

CATALOG NUMBER: P3AS09R359027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142401
5°	138873
10°	126963
15°	107765
20°	85314
25°	64528
30°	46969
35°	31775
40°	19522
45°	11226
50°	6755
55°	5467
60°	4780
65°	4255
70°	3526
75°	3474
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11226 cd/sqm

TEST NUMBER: P1248891

CATALOG NUMBER: P3AS09R359027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	13.2
10°-20°	130.9	29.5
20°-30°	122.4	27.6
30°-40°	74.9	16.9
40°-50°	29.5	6.7
50°-60°	13.0	2.9
60°-70°	8.1	1.8
70°-80°	4.3	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.6	70.3
0°-40°	386.6	87.3
0°-60°	429.1	96.9
0°-90°	443.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	443.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	649	
5°	631	58
15°	475	131
25°	267	122
35°	119	75
45°	36	30
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1248891

CATALOG NUMBER: P3AS09R359027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	649.4
1°	650.0
2°	648.0
3°	643.9
4°	637.8
5°	630.9
6°	622.1
7°	611.8
8°	599.6
9°	585.9
10°	570.2
11°	553.9
12°	536.1
13°	517.0
14°	495.9
15°	474.7
17.5°	420.2
20°	365.6
22.5°	313.1
25°	266.7
27.5°	223.7
30°	185.5
32.5°	150.1
35°	118.7
37.5°	90.7
40°	68.2
42.5°	49.1
45°	36.2
47.5°	25.9
50°	19.8
52.5°	16.4
55°	14.3
57.5°	12.3
60°	10.9
62.5°	9.5
65°	8.2
67.5°	6.8
70°	5.5
72.5°	4.8
75°	4.1
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7



TEST NUMBER: P1248891

CATALOG NUMBER: P3AS09R359027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)