

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247384

Luminaire Tested: P3AS17R509024DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509024DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1278.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247384

CATALOG NUMBER: P3AS17R509024DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1247384

CATALOG NUMBER: P3AS17R509024DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88	85	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75	72	69	67
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72	68	65	64
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68	64	61	60
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	406897
5°	398700
10°	373451
15°	334304
20°	281331
25°	214706
30°	139540
35°	82744
40°	47804
45°	23971
50°	8904
55°	6958
60°	6491
65°	5915
70°	5834
75°	5761
80°	5683
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23971 cd/sqm

TEST NUMBER: P1247384

CATALOG NUMBER: P3AS17R509024DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.5	13.2
10°-20°	407.3	31.9
20°-30°	399.5	31.3
30°-40°	201.3	15.7
40°-50°	63.6	5.0
50°-60°	16.5	1.3
60°-70°	11.7	0.9
70°-80°	7.2	0.6
80°-90°	2.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.3	76.3
0°-40°	1176.6	92.1
0°-60°	1256.7	98.3
0°-90°	1278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1856	
5°	1811	169
15°	1473	407
25°	887	400
35°	309	201
45°	77	64
55°	18	16
65°	11	12
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1247384

CATALOG NUMBER: P3AS17R509024DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1855.6
2.5°	1844.2
5°	1811.3
7.5°	1752.2
10°	1677.2
12.5°	1580.6
15°	1472.6
17.5°	1347.7
20°	1205.6
22.5°	1052.2
25°	887.4
27.5°	712.5
30°	551.1
32.5°	414.7
35°	309.1
37.5°	228.4
40°	167.0
42.5°	118.2
45°	77.3
47.5°	44.3
50°	26.1
52.5°	19.3
55°	18.2
57.5°	15.9
60°	14.8
62.5°	13.6
65°	11.4
67.5°	10.2
70°	9.1
72.5°	8.0
75°	6.8
77.5°	5.7
80°	4.5
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)