

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247387

Luminaire Tested: P3AS17R509024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 488.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247387

CATALOG NUMBER: P3AS17R509024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247387

CATALOG NUMBER: P3AS17R509024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99181
5°	97711
10°	93385
15°	86493
20°	77730
25°	68327
30°	58110
35°	47114
40°	35381
45°	22793
50°	10814
55°	8525
60°	8070
65°	7524
70°	6796
75°	6100
80°	5683
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22793 cd/sqm

TEST NUMBER: P1247387

CATALOG NUMBER: P3AS17R509024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.6	8.5
10°-20°	106.2	21.8
20°-30°	129.1	26.4
30°-40°	109.4	22.4
40°-50°	56.8	11.6
50°-60°	20.5	4.2
60°-70°	14.2	2.9
70°-80°	7.7	1.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.9	56.7
0°-40°	386.3	79.2
0°-60°	463.7	95.0
0°-90°	488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	444	42
15°	381	106
25°	282	129
35°	176	109
45°	74	57
55°	22	21
65°	14	14
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1247387

CATALOG NUMBER: P3AS17R509024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	452.3
2.5°	450.6
5°	443.9
7.5°	433.9
10°	419.4
12.5°	401.0
15°	381.0
17.5°	358.1
20°	333.1
22.5°	307.4
25°	282.4
27.5°	256.2
30°	229.5
32.5°	202.7
35°	176.0
37.5°	149.8
40°	123.6
42.5°	98.6
45°	73.5
47.5°	49.0
50°	31.7
52.5°	24.5
55°	22.3
57.5°	20.1
60°	18.4
62.5°	16.2
65°	14.5
67.5°	12.3
70°	10.6
72.5°	8.9
75°	7.2
77.5°	5.6
80°	4.5
82.5°	3.3
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)