

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248936

Luminaire Tested: P3AS09R459027DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459027DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 764.0 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248936

CATALOG NUMBER: P3AS09R459027DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248936

CATALOG NUMBER: P3AS09R459027DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286907
5°	280189
10°	257555
15°	218231
20°	169321
25°	118362
30°	74568
35°	43902
40°	24847
45°	12063
50°	4196
55°	3403
60°	3289
65°	3165
70°	3077
75°	2881
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12063 cd/sqm

TEST NUMBER: P1248936

CATALOG NUMBER: P3AS09R459027DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	15.4
10°-20°	264.0	34.6
20°-30°	224.2	29.3
30°-40°	106.9	14.0
40°-50°	32.2	4.2
50°-60°	8.2	1.1
60°-70°	6.1	0.8
70°-80°	3.6	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.0	79.3
0°-40°	712.9	93.3
0°-60°	753.3	98.6
0°-90°	764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1308	
5°	1273	118
15°	961	264
25°	489	224
35°	164	107
45°	39	32
55°	9	8
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1248936

CATALOG NUMBER: P3AS09R459027DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1308.4
2.5°	1300.2
5°	1272.9
7.5°	1225.7
10°	1156.7
12.5°	1065.2
15°	961.3
17.5°	845.9
20°	725.6
22.5°	603.3
25°	489.2
27.5°	385.3
30°	294.5
32.5°	221.4
35°	164.0
37.5°	120.9
40°	86.8
42.5°	60.1
45°	38.9
47.5°	21.9
50°	12.3
52.5°	9.6
55°	8.9
57.5°	8.2
60°	7.5
62.5°	6.8
65°	6.1
67.5°	5.5
70°	4.8
72.5°	4.1
75°	3.4
77.5°	2.7
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)