

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247456

Luminaire Tested: P3AS17R609024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 825.9 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247456

CATALOG NUMBER: P3AS17R609024DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1247456

CATALOG NUMBER: P3AS17R609024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209325
5°	204644
10°	191580
15°	171874
20°	147806
25°	122209
30°	96572
35°	71715
40°	49378
45°	30980
50°	17023
55°	9978
60°	8947
65°	7679
70°	6540
75°	6693
80°	5683
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30980 cd/sqm

TEST NUMBER: P1247456

CATALOG NUMBER: P3AS17R609024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.6	10.5
10°-20°	210.3	25.5
20°-30°	230.6	27.9
30°-40°	168.0	20.3
40°-50°	79.4	9.6
50°-60°	26.0	3.1
60°-70°	14.7	1.8
70°-80°	7.9	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.5	63.9
0°-40°	695.5	84.2
0°-60°	800.8	97.0
0°-90°	825.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	825.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	955	
5°	930	87
15°	757	210
25°	505	231
35°	268	168
45°	100	79
55°	26	26
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1247456

CATALOG NUMBER: P3AS17R609024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	954.6
2.5°	949.0
5°	929.7
7.5°	900.2
10°	860.4
12.5°	812.7
15°	757.1
17.5°	697.0
20°	633.4
22.5°	568.7
25°	505.1
27.5°	441.6
30°	381.4
32.5°	323.5
35°	267.9
37.5°	217.9
40°	172.5
42.5°	132.8
45°	99.9
47.5°	72.6
50°	49.9
52.5°	32.9
55°	26.1
57.5°	22.7
60°	20.4
62.5°	17.0
65°	14.8
67.5°	12.5
70°	10.2
72.5°	9.1
75°	7.9
77.5°	5.7
80°	4.5
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0

(END OF REPORT)