

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249030

Luminaire Tested: P3AS09R609027DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249030
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609027DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 244.0 lumens
Efficiency: N/A
Efficacy: 22.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249030

CATALOG NUMBER: P3AS09R609027DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1249030

CATALOG NUMBER: P3AS09R609027DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61837
5°	60444
10°	56601
15°	50783
20°	43660
25°	36099
30°	28536
35°	21174
40°	14599
45°	9148
50°	5049
55°	2944
60°	2631
65°	2283
70°	1923
75°	1949
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9148 cd/sqm

TEST NUMBER: P1249030

CATALOG NUMBER: P3AS09R609027DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	10.5
10°-20°	62.1	25.5
20°-30°	68.1	27.9
30°-40°	49.6	20.3
40°-50°	23.5	9.6
50°-60°	7.7	3.1
60°-70°	4.3	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.8	63.9
0°-40°	205.5	84.2
0°-60°	236.6	97.0
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	282	
5°	275	26
15°	224	62
25°	149	68
35°	79	50
45°	30	23
55°	8	8
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1249030

CATALOG NUMBER: P3AS09R609027DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	282.0
2.5°	280.3
5°	274.6
7.5°	265.9
10°	254.2
12.5°	240.1
15°	223.7
17.5°	205.9
20°	187.1
22.5°	168.0
25°	149.2
27.5°	130.4
30°	112.7
32.5°	95.6
35°	79.1
37.5°	64.4
40°	51.0
42.5°	39.2
45°	29.5
47.5°	21.5
50°	14.8
52.5°	9.7
55°	7.7
57.5°	6.7
60°	6.0
62.5°	5.0
65°	4.4
67.5°	3.7
70°	3.0
72.5°	2.7
75°	2.3
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)