

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249040

Luminaire Tested: P3AS09R659027DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659027DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249040

CATALOG NUMBER: P3AS09R659027DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1249040

CATALOG NUMBER: P3AS09R659027DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95			93
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83			81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77			75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72			70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67			66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63			62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59			58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56			54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206497
5°	194342
10°	191891
15°	188491
20°	177979
25°	165179
30°	128400
35°	74285
40°	29942
45°	13769
50°	5356
55°	2103
60°	1798
65°	1764
70°	1731
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13769 cd/sqm

TEST NUMBER: P1249040

CATALOG NUMBER: P3AS09R659027DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	9.9
10°-20°	231.9	27.4
20°-30°	303.5	35.9
30°-40°	175.8	20.8
40°-50°	37.6	4.5
50°-60°	6.1	0.7
60°-70°	3.4	0.4
70°-80°	2.0	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.3	73.3
0°-40°	795.2	94.1
0°-60°	838.9	99.3
0°-90°	845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	942	
5°	883	84
15°	830	232
25°	683	304
35°	278	176
45°	44	38
55°	6	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1249040

CATALOG NUMBER: P3AS09R659027DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	941.7
2.5°	915.1
5°	882.9
7.5°	870.0
10°	861.8
12.5°	850.1
15°	830.3
17.5°	799.6
20°	762.7
22.5°	727.8
25°	682.7
27.5°	606.9
30°	507.1
32.5°	392.9
35°	277.5
37.5°	175.6
40°	104.6
42.5°	65.6
45°	44.4
47.5°	28.7
50°	15.7
52.5°	7.5
55°	5.5
57.5°	4.8
60°	4.1
62.5°	4.1
65°	3.4
67.5°	2.7
70°	2.7
72.5°	2.1
75°	2.1
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)