

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249068

Luminaire Tested: P3AS09R709027DE010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1249068  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709027DE010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 855.0 lumens  
Efficiency: N/A  
Efficacy: 77.0 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1249068  
CATALOG NUMBER: P3AS09R709027DE010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1249068

CATALOG NUMBER: P3AS09R709027DE010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	169789
5°	162007
10°	154150
15°	150012
20°	144469
25°	136726
30°	127184
35°	106836
40°	68843
45°	32003
50°	8392
55°	2103
60°	2105
65°	1764
70°	1731
75°	1779
80°	1768
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 32003 cd/sqm



TEST NUMBER: P1249068  
 CATALOG NUMBER: P3AS09R709027DE010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.9	8.1
10°-20°	185.7	21.7
20°-30°	259.4	30.3
30°-40°	240.5	28.1
40°-50°	86.2	10.1
50°-60°	7.3	0.9
60°-70°	3.6	0.4
70°-80°	2.4	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.0	60.1
0°-40°	754.5	88.2
0°-60°	848.1	99.2
0°-90°	855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	774	
5°	736	69
15°	661	186
25°	565	259
35°	399	241
45°	103	86
55°	6	7
65°	3	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1249068  
CATALOG NUMBER: P3AS09R709027DE010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	774.3
2.5°	762.6
5°	736.0
7.5°	711.4
10°	692.3
12.5°	676.5
15°	660.8
17.5°	641.7
20°	619.1
22.5°	593.2
25°	565.1
27.5°	536.4
30°	502.3
32.5°	458.5
35°	399.1
37.5°	323.2
40°	240.5
42.5°	164.0
45°	103.2
47.5°	57.4
50°	24.6
52.5°	8.2
55°	5.5
57.5°	4.8
60°	4.8
62.5°	4.1
65°	3.4
67.5°	3.4
70°	2.7
72.5°	2.7
75°	2.1
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)