

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247557

Luminaire Tested: P3AS20R209024D010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247557  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209024D010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1543.0 lumens  
Efficiency: N/A  
Efficacy: 53.6 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247557  
CATALOG NUMBER: P3AS20R209024D010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1247557  
 CATALOG NUMBER: P3AS20R209024D010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1187164
5°	1079152
10°	797558
15°	493374
20°	281751
25°	160848
30°	90216
35°	49068
40°	26879
45°	14792
50°	8631
55°	6270
60°	5877
65°	5396
70°	4809
75°	5083
80°	3788
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14792 cd/sqm



TEST NUMBER: P1247557  
 CATALOG NUMBER: P3AS20R209024D010 E3DL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	424.5	27.5
10°-20°	606.1	39.3
20°-30°	316.3	20.5
30°-40°	122.3	7.9
40°-50°	39.7	2.6
50°-60°	15.6	1.0
60°-70°	10.3	0.7
70°-80°	6.1	0.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1346.9	87.3
0°-40°	1469.3	95.2
0°-60°	1524.6	98.8
0°-90°	1543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1543.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5414	
5°	4903	425
15°	2173	606
25°	665	316
35°	183	122
45°	48	40
55°	16	16
65°	10	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1247557  
CATALOG NUMBER: P3AS20R209024D010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5413.9
1°	5403.5
2°	5339.4
3°	5241.0
4°	5088.9
5°	4902.6
6°	4682.0
7°	4437.5
8°	4154.3
9°	3878.6
10°	3581.9
12.5°	2847.1
15°	2173.3
17.5°	1626.3
20°	1207.4
22.5°	894.4
25°	664.8
27.5°	490.4
30°	356.3
32.5°	257.9
35°	183.3
37.5°	132.7
40°	93.9
42.5°	67.1
45°	47.7
47.5°	34.3
50°	25.3
52.5°	19.4
55°	16.4
57.5°	14.9
60°	13.4
62.5°	11.9
65°	10.4
67.5°	8.9
70°	7.5
72.5°	7.5
75°	6.0
77.5°	4.5
80°	3.0
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)