

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247668

Luminaire Tested: P3AS20R409024D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409024D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2087.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247668

CATALOG NUMBER: P3AS20R409024D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1247668

CATALOG NUMBER: P3AS20R409024D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93	91	90	88
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90	88	86	85
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88	85	83	82
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85	82	80	79
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82	79	77	76
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79	76	74	73
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77	74	71	70
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1063796
5°	1056106
10°	1028460
15°	918711
20°	609170
25°	228207
30°	61047
35°	23851
40°	8588
45°	4093
50°	1262
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4093 cd/sqm

TEST NUMBER: P1247668

CATALOG NUMBER: P3AS20R409024D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.8	21.7
10°-20°	1072.3	51.4
20°-30°	486.3	23.3
30°-40°	63.0	3.0
40°-50°	10.9	0.5
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2011.3	96.4
0°-40°	2074.3	99.4
0°-60°	2086.6	100.0
0°-90°	2087.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2087.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4851	
5°	4798	453
15°	4047	1072
25°	943	486
35°	89	63
45°	13	11
55°	2	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247668

CATALOG NUMBER: P3AS20R409024D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4851.3
1°	4848.4
2°	4841.1
3°	4830.1
4°	4816.2
5°	4797.9
6°	4776.8
7°	4750.5
8°	4718.3
9°	4674.5
10°	4618.9
11°	4553.9
12°	4467.0
13°	4359.6
14°	4219.3
15°	4046.9
16°	3827.0
17°	3576.4
18°	3275.3
19°	2957.5
20°	2610.5
21°	2263.4
22°	1921.5
23°	1581.0
24°	1246.4
25°	943.2
26°	698.5
27°	511.4
28°	384.3
29°	298.8
30°	241.1
31°	199.5
32°	166.6
32.5°	152.0
33°	137.4
34°	111.8
35°	89.1
36°	70.1
37°	55.5
37.5°	49.7
38°	43.8
39°	36.5
40°	30.0
42.5°	19.7
45°	13.2



TEST NUMBER: P1247668
CATALOG NUMBER: P3AS20R409024D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.0
50°	3.7
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)