

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249165

Luminaire Tested: P3AS13R159027DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1249165  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R159027DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 942.0 lumens  
Efficiency: N/A  
Efficacy: 64.5 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1249165  
CATALOG NUMBER: P3AS13R159027DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1249165  
 CATALOG NUMBER: P3AS13R159027DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	804716
5°	714306
10°	496050
15°	293350
20°	167081
25°	95497
30°	52844
35°	28188
40°	15572
45°	8435
50°	5254
55°	4167
60°	3596
65°	3321
70°	2885
75°	3050
80°	2273
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8435 cd/sqm



TEST NUMBER: P1249165  
 CATALOG NUMBER: P3AS13R159027DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	275.9	29.3
10°-20°	364.2	38.7
20°-30°	187.5	19.9
30°-40°	70.4	7.5
40°-50°	23.0	2.4
50°-60°	9.9	1.1
60°-70°	6.3	0.7
70°-80°	3.7	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.7	87.9
0°-40°	898.1	95.3
0°-60°	931.0	98.8
0°-90°	942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3670	
5°	3245	276
15°	1292	364
25°	395	188
35°	105	70
45°	27	23
55°	11	10
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1249165  
CATALOG NUMBER: P3AS13R159027DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3669.8
1°	3662.5
2°	3614.4
3°	3522.8
4°	3402.1
5°	3245.1
6°	3067.2
7°	2872.1
8°	2655.2
9°	2441.1
10°	2227.8
12.5°	1714.2
15°	1292.2
17.5°	967.4
20°	716.0
22.5°	534.5
25°	394.7
27.5°	287.7
30°	208.7
32.5°	147.9
35°	105.3
37.5°	75.3
40°	54.4
42.5°	39.0
45°	27.2
47.5°	20.0
50°	15.4
52.5°	12.7
55°	10.9
57.5°	9.1
60°	8.2
62.5°	7.3
65°	6.4
67.5°	5.4
70°	4.5
72.5°	4.5
75°	3.6
77.5°	2.7
80°	1.8
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)