

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247688

Luminaire Tested: P3AS20R409024D010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409024D010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1737.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247688

CATALOG NUMBER: P3AS20R409024D010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1247688

CATALOG NUMBER: P3AS20R409024D010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	768601
5°	746267
10°	677231
15°	559481
20°	403585
25°	249619
30°	135135
35°	69841
40°	37985
45°	21274
50°	10678
55°	7990
60°	7192
65°	6953
70°	6668
75°	6354
80°	5683
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21274 cd/sqm

TEST NUMBER: P1247688

CATALOG NUMBER: P3AS20R409024D010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.5	18.0
10°-20°	671.1	38.6
20°-30°	478.9	27.6
30°-40°	176.3	10.1
40°-50°	55.5	3.2
50°-60°	19.3	1.1
60°-70°	13.3	0.8
70°-80°	7.9	0.5
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1462.5	84.2
0°-40°	1638.8	94.3
0°-60°	1713.6	98.7
0°-90°	1737.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1737.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3505	
5°	3390	313
15°	2464	671
25°	1032	479
35°	261	176
45°	69	56
55°	21	19
65°	13	13
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1247688

CATALOG NUMBER: P3AS20R409024D010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3505.1
2.5°	3478.3
5°	3390.3
7.5°	3244.2
10°	3041.5
12.5°	2783.5
15°	2464.5
17.5°	2106.7
20°	1729.5
22.5°	1358.2
25°	1031.7
27.5°	757.4
30°	533.7
32.5°	374.2
35°	260.9
37.5°	184.9
40°	132.7
42.5°	95.4
45°	68.6
47.5°	46.2
50°	31.3
52.5°	22.4
55°	20.9
57.5°	19.4
60°	16.4
62.5°	14.9
65°	13.4
67.5°	11.9
70°	10.4
72.5°	8.9
75°	7.5
77.5°	6.0
80°	4.5
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)