

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247753

Luminaire Tested: P3AS20R559024D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559024D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1924.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247753
CATALOG NUMBER: P3AS20R559024D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247753
 CATALOG NUMBER: P3AS20R559024D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.6	12.3
10°-20°	674.0	35.0
20°-30°	749.2	38.9
30°-40°	233.2	12.1
40°-50°	28.0	1.5
50°-60°	2.2	0.1
60°-70°	0.7	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1659.8	86.3
0°-40°	1893.0	98.4
0°-60°	1923.2	100.0
0°-90°	1924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1924.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2544	
5°	2445	237
15°	2421	674
25°	1700	749
35°	312	233
45°	33	28
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1247753
CATALOG NUMBER: P3AS20R559024D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2544.4
1°	2534.9
2°	2510.0
3°	2479.3
4°	2451.6
5°	2445.0
6°	2452.3
7°	2467.7
8°	2485.2
9°	2499.1
10°	2503.5
11°	2500.5
12°	2488.9
13°	2470.6
14°	2449.4
15°	2420.9
16°	2388.0
17°	2346.3
18°	2299.5
19°	2243.3
20°	2179.7
21°	2107.3
22°	2021.8
23°	1927.5
24°	1819.3
25°	1700.2
26°	1569.3
27°	1430.4
28°	1282.1
29°	1129.3
30°	973.6
31°	817.2
32°	664.4
32.5°	596.4
33°	526.3
34°	407.1
35°	312.1
36°	237.6
37°	176.2
37.5°	150.6
38°	130.8
39°	99.4
40°	80.4
42.5°	51.2
45°	32.9



TEST NUMBER: P1247753
CATALOG NUMBER: P3AS20R559024D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.7
50°	8.8
52.5°	2.9
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)