

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247755

Luminaire Tested: P3AS20R559024D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559024D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 27.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247755

CATALOG NUMBER: P3AS20R559024D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247755

CATALOG NUMBER: P3AS20R559024D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218579
5°	216354
10°	208947
15°	193123
20°	166661
25°	131621
30°	93381
35°	60204
40°	36153
45°	20374
50°	10951
55°	3900
60°	3508
65°	3424
70°	3270
75°	3135
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20374 cd/sqm

TEST NUMBER: P1247755

CATALOG NUMBER: P3AS20R559024D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	11.6
10°-20°	235.2	29.6
20°-30°	246.5	31.0
30°-40°	143.8	18.1
40°-50°	53.8	6.8
50°-60°	12.7	1.6
60°-70°	6.5	0.8
70°-80°	3.9	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	72.1
0°-40°	718.1	90.2
0°-60°	784.6	98.6
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	997	
5°	983	92
15°	851	235
25°	544	247
35°	225	144
45°	66	54
55°	10	13
65°	7	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1247755

CATALOG NUMBER: P3AS20R559024D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	996.8
2.5°	993.9
5°	982.9
7.5°	965.4
10°	938.4
12.5°	900.4
15°	850.7
17.5°	787.9
20°	714.2
22.5°	631.7
25°	544.0
27.5°	454.2
30°	368.8
32.5°	291.4
35°	224.9
37.5°	170.9
40°	126.3
42.5°	90.6
45°	65.7
47.5°	47.5
50°	32.1
52.5°	18.3
55°	10.2
57.5°	8.8
60°	8.0
62.5°	7.3
65°	6.6
67.5°	5.8
70°	5.1
72.5°	4.4
75°	3.7
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)