

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247787

Luminaire Tested: P3AS20R609024D010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1247787  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R609024D010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1568.0 lumens  
Efficiency: N/A  
Efficacy: 54.4 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247787

CATALOG NUMBER: P3AS20R609024D010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1247787

CATALOG NUMBER: P3AS20R609024D010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 84  | 91  | 86  | 83  |  | 88  | 85  | 82  |  | 86  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 81  | 77  | 85  | 80  | 76  |  | 83  | 79  | 75  |  | 81  |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  |  | 78  | 73  | 70  |  | 76  |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  |  | 73  | 68  | 65  |  | 72  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  |  | 69  | 64  | 60  |  | 67  |
| 8   | 77  | 68  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  |  | 65  | 60  | 56  |  | 64  |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |
| 10  | 70  | 60  | 54  | 50  | 69  | 60  | 54  | 50  | 59  | 53  | 50  |  | 58  | 53  | 50  |  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 370255 |
| 5°  | 366739 |
| 10° | 356061 |
| 15° | 333577 |
| 20° | 295262 |
| 25° | 247006 |
| 30° | 193574 |
| 35° | 140431 |
| 40° | 93432  |
| 45° | 58239  |
| 50° | 31521  |
| 55° | 9099   |
| 60° | 8508   |
| 65° | 7731   |
| 70° | 7629   |
| 75° | 7540   |
| 80° | 7577   |
| 85° | 7548   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 58239 cd/sqm

TEST NUMBER: P1247787

CATALOG NUMBER: P3AS20R609024D010 E3DL1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 156.9  | 10.0      |
| 10°-20°   | 407.7  | 26.0      |
| 20°-30°   | 464.7  | 29.6      |
| 30°-40°   | 329.5  | 21.0      |
| 40°-50°   | 149.5  | 9.5       |
| 50°-60°   | 31.7   | 2.0       |
| 60°-70°   | 15.3   | 1.0       |
| 70°-80°   | 9.4    | 0.6       |
| 80°-90°   | 3.3    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1029.2 | 65.6      |
| 0°-40°    | 1358.8 | 86.7      |
| 0°-60°    | 1540.0 | 98.2      |
| 0°-90°    | 1568.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1568.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1688 |      |
| 5°  | 1666 | 157  |
| 15° | 1469 | 408  |
| 25° | 1021 | 465  |
| 35° | 525  | 330  |
| 45° | 188  | 150  |
| 55° | 24   | 32   |
| 65° | 15   | 15   |
| 75° | 9    | 9    |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1247787

CATALOG NUMBER: P3AS20R609024D010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1688.5 |
| 2.5°  | 1682.5 |
| 5°    | 1666.1 |
| 7.5°  | 1637.8 |
| 10°   | 1599.1 |
| 12.5° | 1543.9 |
| 15°   | 1469.4 |
| 17.5° | 1375.5 |
| 20°   | 1265.3 |
| 22.5° | 1146.0 |
| 25°   | 1020.9 |
| 27.5° | 892.7  |
| 30°   | 764.5  |
| 32.5° | 642.3  |
| 35°   | 524.6  |
| 37.5° | 420.3  |
| 40°   | 326.4  |
| 42.5° | 247.4  |
| 45°   | 187.8  |
| 47.5° | 140.1  |
| 50°   | 92.4   |
| 52.5° | 43.2   |
| 55°   | 23.8   |
| 57.5° | 20.9   |
| 60°   | 19.4   |
| 62.5° | 17.9   |
| 65°   | 14.9   |
| 67.5° | 13.4   |
| 70°   | 11.9   |
| 72.5° | 10.4   |
| 75°   | 8.9    |
| 77.5° | 7.5    |
| 80°   | 6.0    |
| 82.5° | 4.5    |
| 85°   | 3.0    |
| 87.5° | 1.5    |
| 90°   | 0.0    |

(END OF REPORT)