

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249276

Luminaire Tested: P3AS13R359027DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359027DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1151.9 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249276

CATALOG NUMBER: P3AS13R359027DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1249276

CATALOG NUMBER: P3AS13R359027DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	98	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	751190
5°	735877
10°	684601
15°	501910
20°	257016
25°	92618
30°	36056
35°	12635
40°	5181
45°	1395
50°	1228
55°	1376
60°	1184
65°	934
70°	1154
75°	1525
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 1525 cd/sqm

TEST NUMBER: P1249276

CATALOG NUMBER: P3AS13R359027DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.7	27.1
10°-20°	584.8	50.8
20°-30°	207.0	18.0
30°-40°	36.3	3.1
40°-50°	5.3	0.5
50°-60°	2.9	0.3
60°-70°	2.1	0.2
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1103.4	95.8
0°-40°	1139.7	98.9
0°-60°	1147.9	99.7
0°-90°	1151.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1151.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3426	
5°	3343	312
15°	2211	585
25°	383	207
35°	47	36
45°	4	5
55°	4	3
65°	2	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1249276

CATALOG NUMBER: P3AS13R359027DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3425.7
1°	3424.7
2°	3413.9
3°	3393.0
4°	3373.9
5°	3343.1
6°	3311.3
7°	3276.0
8°	3232.4
9°	3164.4
10°	3074.6
11°	2950.3
12°	2800.6
13°	2622.8
14°	2426.8
15°	2210.9
17.5°	1646.6
20°	1101.4
22.5°	664.1
25°	382.8
27.5°	228.6
30°	142.4
32.5°	82.6
35°	47.2
37.5°	29.9
40°	18.1
42.5°	9.1
45°	4.5
47.5°	3.6
50°	3.6
52.5°	3.6
55°	3.6
57.5°	2.7
60°	2.7
62.5°	2.7
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0



TEST NUMBER: P1249276

CATALOG NUMBER: P3AS13R359027DE010 E3CB1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)