

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247814

Luminaire Tested: P3AS20R659024D010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659024D010 E3DL1H
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1495.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247814
CATALOG NUMBER: P3AS20R659024D010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1247814
 CATALOG NUMBER: P3AS20R659024D010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	352559
5°	348337
10°	335108
15°	313918
20°	282358
25°	239748
30°	187523
35°	133632
40°	87450
45°	54052
50°	27462
55°	9672
60°	8508
65°	8509
70°	7629
75°	7540
80°	7577
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54052 cd/sqm



TEST NUMBER: P1247814
 CATALOG NUMBER: P3AS20R659024D010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	9.9
10°-20°	384.9	25.7
20°-30°	449.8	30.1
30°-40°	314.3	21.0
40°-50°	138.3	9.3
50°-60°	30.8	2.1
60°-70°	15.7	1.0
70°-80°	9.4	0.6
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	983.2	65.8
0°-40°	1297.5	86.8
0°-60°	1466.7	98.1
0°-90°	1495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1608	
5°	1582	149
15°	1383	385
25°	991	450
35°	499	314
45°	174	138
55°	25	31
65°	16	16
75°	9	9
85°	3	3
90°	0	



TEST NUMBER: P1247814
CATALOG NUMBER: P3AS20R659024D010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1607.8
2.5°	1601.9
5°	1582.5
7.5°	1549.7
10°	1505.0
12.5°	1449.9
15°	1382.8
17.5°	1300.9
20°	1210.0
22.5°	1107.1
25°	990.9
27.5°	868.7
30°	740.6
32.5°	616.9
35°	499.2
37.5°	396.4
40°	305.5
42.5°	231.0
45°	174.3
47.5°	128.1
50°	80.5
52.5°	41.7
55°	25.3
57.5°	22.4
60°	19.4
62.5°	17.9
65°	16.4
67.5°	13.4
70°	11.9
72.5°	10.4
75°	8.9
77.5°	7.5
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)