

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247819

Luminaire Tested: P3AS20R659024D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247819  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R659024D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 576.0 lumens  
Efficiency: N/A  
Efficacy: 20.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247819  
CATALOG NUMBER: P3AS20R659024D010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1247819

CATALOG NUMBER: P3AS20R659024D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	102492
5°	101122
10°	97727
15°	92169
20°	85011
25°	77158
30°	68340
35°	58170
40°	46287
45°	32655
50°	18967
55°	10360
60°	9604
65°	8717
70°	7950
75°	7456
80°	6440
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 32655 cd/sqm



TEST NUMBER: P1247819  
 CATALOG NUMBER: P3AS20R659024D010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.2	7.5
10°-20°	113.6	19.7
20°-30°	146.0	25.3
30°-40°	135.1	23.4
40°-50°	81.5	14.2
50°-60°	27.8	4.8
60°-70°	16.7	2.9
70°-80°	9.5	1.6
80°-90°	2.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	302.8	52.6
0°-40°	437.8	76.0
0°-60°	547.1	95.0
0°-90°	576.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	467	
5°	459	43
15°	406	114
25°	319	146
35°	217	135
45°	105	81
55°	27	28
65°	17	17
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1247819  
CATALOG NUMBER: P3AS20R659024D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	467.4
2.5°	465.3
5°	459.4
7.5°	450.6
10°	438.9
12.5°	424.3
15°	406.0
17.5°	386.2
20°	364.3
22.5°	341.6
25°	318.9
27.5°	294.8
30°	269.9
32.5°	245.1
35°	217.3
37.5°	190.2
40°	161.7
42.5°	133.1
45°	105.3
47.5°	79.7
50°	55.6
52.5°	35.1
55°	27.1
57.5°	24.1
60°	21.9
62.5°	19.0
65°	16.8
67.5°	14.6
70°	12.4
72.5°	11.0
75°	8.8
77.5°	7.3
80°	5.1
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)