

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249330

Luminaire Tested: P3AS13R409027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 667.0 lumens
Efficiency: N/A
Efficacy: 45.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249330

CATALOG NUMBER: P3AS13R409027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1249330

CATALOG NUMBER: P3AS13R409027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207681
5°	203477
10°	189464
15°	165131
20°	133082
25°	99756
30°	70137
35°	45936
40°	27824
45°	16622
50°	9927
55°	7990
60°	7149
65°	6123
70°	5834
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16622 cd/sqm

TEST NUMBER: P1249330

CATALOG NUMBER: P3AS13R409027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	12.9
10°-20°	200.3	30.0
20°-30°	188.8	28.3
30°-40°	109.2	16.4
40°-50°	43.5	6.5
50°-60°	19.3	2.9
60°-70°	11.9	1.8
70°-80°	6.2	0.9
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.0	71.2
0°-40°	584.2	87.6
0°-60°	646.9	97.0
0°-90°	667.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	667.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	947	
5°	924	86
15°	727	200
25°	412	189
35°	172	109
45°	54	43
55°	21	19
65°	12	12
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249330

CATALOG NUMBER: P3AS13R409027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	947.1
2.5°	941.7
5°	924.4
7.5°	892.6
10°	850.9
12.5°	794.6
15°	727.4
17.5°	652.0
20°	570.3
22.5°	488.6
25°	412.3
27.5°	341.4
30°	277.0
32.5°	220.7
35°	171.6
37.5°	129.9
40°	97.2
42.5°	72.6
45°	53.6
47.5°	39.0
50°	29.1
52.5°	23.6
55°	20.9
57.5°	19.1
60°	16.3
62.5°	13.6
65°	11.8
67.5°	10.0
70°	9.1
72.5°	7.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)