

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249362

Luminaire Tested: P3AS13R509027DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509027DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1260.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249362
CATALOG NUMBER: P3AS13R509027DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1249362
 CATALOG NUMBER: P3AS13R509027DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440316
5°	428592
10°	409010
15°	370263
20°	320348
25°	262757
30°	150935
35°	46900
40°	12595
45°	4404
50°	1058
55°	344
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4404 cd/sqm



TEST NUMBER: P1249362
 CATALOG NUMBER: P3AS13R509027DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.4	14.5
10°-20°	451.9	35.9
20°-30°	475.0	37.7
30°-40°	136.0	10.8
40°-50°	13.3	1.1
50°-60°	1.1	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1109.3	88.0
0°-40°	1245.3	98.8
0°-60°	1259.6	100.0
0°-90°	1260.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1260.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2008	
5°	1947	182
15°	1631	452
25°	1086	475
35°	175	136
45°	14	13
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1249362
CATALOG NUMBER: P3AS13R509027DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2008.0
1°	2004.9
2°	1996.0
3°	1983.1
4°	1965.8
5°	1947.1
6°	1927.1
7°	1905.8
8°	1885.8
9°	1862.7
10°	1836.9
11°	1807.1
12°	1772.9
13°	1730.2
14°	1683.9
15°	1631.0
16°	1575.0
17°	1520.8
18°	1465.2
19°	1416.3
20°	1372.8
21°	1331.0
22°	1283.4
23°	1228.7
24°	1164.7
25°	1086.0
26°	1000.7
27°	905.5
28°	810.9
29°	708.6
30°	596.1
31°	490.8
32°	393.9
32.5°	351.6
33°	309.0
34°	236.9
35°	175.2
36°	128.5
37°	95.6
37.5°	82.7
38°	71.6
39°	55.6
40°	44.0
42.5°	24.9
45°	14.2



TEST NUMBER: P1249362
CATALOG NUMBER: P3AS13R509027DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.0
50°	3.1
52.5°	1.3
55°	0.9
57.5°	0.9
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)