

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247826

Luminaire Tested: P3AS20R659024D010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659024D010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1033.0 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247826

CATALOG NUMBER: P3AS20R659024D010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1247826

CATALOG NUMBER: P3AS20R659024D010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262567
5°	256042
10°	238428
15°	213690
20°	184536
25°	153517
30°	121057
35°	89704
40°	61830
45°	38330
50°	20844
55°	13113
60°	11096
65°	10066
70°	8591
75°	7540
80°	7577
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38330 cd/sqm

TEST NUMBER: P1247826

CATALOG NUMBER: P3AS20R659024D010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	10.5
10°-20°	261.6	25.3
20°-30°	289.3	28.0
30°-40°	210.1	20.3
40°-50°	98.4	9.5
50°-60°	33.2	3.2
60°-70°	19.1	1.9
70°-80°	10.0	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	658.9	63.8
0°-40°	869.0	84.1
0°-60°	1000.6	96.9
0°-90°	1033.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1197	
5°	1163	108
15°	941	262
25°	634	289
35°	335	210
45°	124	98
55°	34	33
65°	19	19
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1247826

CATALOG NUMBER: P3AS20R659024D010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1197.4
2.5°	1190.0
5°	1163.2
7.5°	1123.0
10°	1070.8
12.5°	1009.8
15°	941.3
17.5°	866.8
20°	790.8
22.5°	711.9
25°	634.5
27.5°	555.5
30°	478.1
32.5°	403.6
35°	335.1
37.5°	272.5
40°	216.0
42.5°	165.3
45°	123.6
47.5°	89.4
50°	61.1
52.5°	41.7
55°	34.3
57.5°	29.8
60°	25.3
62.5°	22.3
65°	19.4
67.5°	16.4
70°	13.4
72.5°	11.9
75°	8.9
77.5°	7.4
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)