

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247848

Luminaire Tested: P3AS20R709024D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709024D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 525.0 lumens
Efficiency: N/A
Efficacy: 18.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247848

CATALOG NUMBER: P3AS20R709024D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247848

CATALOG NUMBER: P3AS20R709024D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123148
5°	120889
10°	113981
15°	103451
20°	90495
25°	76335
30°	62491
35°	48479
40°	34694
45°	21956
50°	10951
55°	6690
60°	5745
65°	5292
70°	4680
75°	4321
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21956 cd/sqm

TEST NUMBER: P1247848

CATALOG NUMBER: P3AS20R709024D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.2	9.8
10°-20°	126.8	24.2
20°-30°	144.4	27.5
30°-40°	112.9	21.5
40°-50°	55.5	10.6
50°-60°	17.0	3.2
60°-70°	10.1	1.9
70°-80°	5.4	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.5	61.4
0°-40°	435.4	82.9
0°-60°	507.9	96.7
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	549	51
15°	456	127
25°	316	144
35°	181	113
45°	71	55
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1247848

CATALOG NUMBER: P3AS20R709024D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	561.6
2.5°	558.7
5°	549.2
7.5°	533.8
10°	511.9
12.5°	486.4
15°	455.7
17.5°	422.8
20°	387.8
22.5°	351.3
25°	315.5
27.5°	280.4
30°	246.8
32.5°	213.2
35°	181.1
37.5°	150.4
40°	121.2
42.5°	94.2
45°	70.8
47.5°	49.7
50°	32.1
52.5°	21.2
55°	17.5
57.5°	15.3
60°	13.1
62.5°	11.7
65°	10.2
67.5°	8.8
70°	7.3
72.5°	5.8
75°	5.1
77.5°	4.4
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)