

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247923

Luminaire Tested: P3AS02R109027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 44.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247923

CATALOG NUMBER: P3AS02R109027DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1247923

CATALOG NUMBER: P3AS02R109027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	107	104		110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	96	92		104	99	95	91		95	92	89		92	90	87		90	87	85
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	86	80	75		92	85	79	74		82	77	73		80	76	73		78	75	72
5	89	80	73	68		87	79	73	68		77	72	67		75	71	67		74	69	66
6	84	74	68	63		83	73	67	63		72	66	62		70	66	62		69	65	61
7	80	69	63	58		78	69	63	58		67	62	58		66	61	57		65	61	57
8	76	65	59	54		74	65	58	54		63	58	54		62	57	54		61	57	53
9	72	61	55	51		71	61	55	51		60	54	50		59	54	50		58	53	50
10	68	58	52	48		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42628
5°	41470
10°	37897
15°	33190
20°	28469
25°	23784
30°	19016
35°	14268
40°	10362
45°	6760
50°	4230
55°	2867
60°	2544
65°	2335
70°	2180
75°	2033
80°	1894
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6760 cd/sqm

TEST NUMBER: P1247923

CATALOG NUMBER: P3AS02R109027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	10.3
10°-20°	40.7	24.1
20°-30°	44.9	26.6
30°-40°	33.6	19.9
40°-50°	17.4	10.3
50°-60°	7.2	4.3
60°-70°	4.5	2.6
70°-80°	2.5	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.0	61.0
0°-40°	136.6	80.9
0°-60°	161.3	95.4
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	194	
5°	188	17
15°	146	41
25°	98	45
35°	53	34
45°	22	17
55°	8	7
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1247923

CATALOG NUMBER: P3AS02R109027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	194.4
1°	194.6
2°	194.0
3°	192.7
4°	190.8
5°	188.4
6°	185.4
7°	182.2
8°	178.3
9°	174.3
10°	170.2
12.5°	158.4
15°	146.2
17.5°	134.0
20°	122.0
22.5°	109.8
25°	98.3
27.5°	86.7
30°	75.1
32.5°	63.8
35°	53.3
37.5°	44.3
40°	36.2
42.5°	28.7
45°	21.8
47.5°	16.5
50°	12.4
52.5°	9.2
55°	7.5
57.5°	6.6
60°	5.8
62.5°	5.1
65°	4.5
67.5°	3.9
70°	3.4
72.5°	2.8
75°	2.4
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)