

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248009

Luminaire Tested: P3AS02R209027DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209027DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 235.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248009

CATALOG NUMBER: P3AS02R209027DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248009

CATALOG NUMBER: P3AS02R209027DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	100		108	104	101	98		101	98	96		98	96	94		95	94	92
3	106	100	96	93		104	99	95	92		97	93	91		94	92	89		92	90	88
4	102	96	91	88		100	95	90	87		92	89	86		91	88	85		89	86	84
5	98	91	87	83		97	90	86	83		89	85	82		87	84	81		86	83	81
6	95	87	83	79		93	87	82	79		85	81	78		84	81	78		83	80	77
7	91	84	79	76		90	83	79	76		82	78	75		81	78	75		80	77	75
8	88	81	76	73		87	80	76	73		79	75	72		78	75	72		77	74	72
9	85	78	73	70		85	77	73	70		77	73	70		76	72	69		75	72	69
10	83	75	71	68		82	75	70	67		74	70	67		73	70	67		73	69	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	180797
5°	164362
10°	121463
15°	75142
20°	42914
25°	24509
30°	13749
35°	7469
40°	4093
45°	2264
50°	1330
55°	956
60°	877
65°	830
70°	705
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2264 cd/sqm

TEST NUMBER: P1248009

CATALOG NUMBER: P3AS02R209027DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	27.5
10°-20°	92.3	39.3
20°-30°	48.2	20.5
30°-40°	18.6	7.9
40°-50°	6.0	2.6
50°-60°	2.4	1.0
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.1	87.3
0°-40°	223.8	95.2
0°-60°	232.2	98.8
0°-90°	235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	824	
5°	747	65
15°	331	92
25°	101	48
35°	28	19
45°	7	6
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248009

CATALOG NUMBER: P3AS02R209027DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	824.5
1°	823.0
2°	813.2
3°	798.2
4°	775.0
5°	746.7
6°	713.1
7°	675.8
8°	632.7
9°	590.7
10°	545.5
12.5°	433.6
15°	331.0
17.5°	247.7
20°	183.9
22.5°	136.2
25°	101.3
27.5°	74.7
30°	54.3
32.5°	39.3
35°	27.9
37.5°	20.2
40°	14.3
42.5°	10.2
45°	7.3
47.5°	5.2
50°	3.9
52.5°	3.0
55°	2.5
57.5°	2.3
60°	2.0
62.5°	1.8
65°	1.6
67.5°	1.4
70°	1.1
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)