

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249423

Luminaire Tested: P3AS13R609027DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609027DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1086.9 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249423
CATALOG NUMBER: P3AS13R609027DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1249423
 CATALOG NUMBER: P3AS13R609027DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284802
5°	268874
10°	261874
15°	255893
20°	237927
25°	212698
30°	162455
35°	93799
40°	36411
45°	15164
50°	3343
55°	497
60°	395
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15164 cd/sqm



TEST NUMBER: P1249423
 CATALOG NUMBER: P3AS13R609027DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	10.6
10°-20°	314.0	28.9
20°-30°	393.3	36.2
30°-40°	219.8	20.2
40°-50°	41.8	3.8
50°-60°	2.1	0.2
60°-70°	0.5	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	822.6	75.7
0°-40°	1042.4	95.9
0°-60°	1086.3	99.9
0°-90°	1086.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1086.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1299	
5°	1222	115
15°	1127	314
25°	879	393
35°	350	220
45°	49	42
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1249423
CATALOG NUMBER: P3AS13R609027DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1298.8
1°	1293.5
2°	1276.6
3°	1256.6
4°	1237.9
5°	1221.5
6°	1209.0
7°	1198.3
8°	1190.3
9°	1182.8
10°	1176.1
11°	1169.4
12°	1161.9
13°	1152.5
14°	1141.4
15°	1127.2
16°	1109.9
17°	1090.3
18°	1068.1
19°	1042.7
20°	1019.6
21°	994.7
22°	968.9
23°	941.8
24°	912.0
25°	879.1
26°	840.4
27°	797.3
28°	748.8
29°	697.2
30°	641.6
31°	585.6
32°	527.8
32.5°	496.2
33°	467.8
34°	408.6
35°	350.4
36°	297.9
37°	242.3
37.5°	217.0
38°	192.1
39°	154.7
40°	127.2
42.5°	77.4
45°	48.9



TEST NUMBER: P1249423
CATALOG NUMBER: P3AS13R609027DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	27.1
50°	9.8
52.5°	2.2
55°	1.3
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)