

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248074

Luminaire Tested: P3AS02R309027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 185.0 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248074

CATALOG NUMBER: P3AS02R309027DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248074

CATALOG NUMBER: P3AS02R309027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76		
4	94	86	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43703
5°	42725
10°	39723
15°	35346
20°	30406
25°	25768
30°	21370
35°	16784
40°	12023
45°	7877
50°	4503
55°	2944
60°	2807
65°	2594
70°	2308
75°	2118
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7877 cd/sqm

TEST NUMBER: P1248074

CATALOG NUMBER: P3AS02R309027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.0	9.7
10°-20°	43.3	23.4
20°-30°	48.8	26.4
30°-40°	39.0	21.1
40°-50°	20.0	10.8
50°-60°	7.5	4.1
60°-70°	4.9	2.7
70°-80°	2.7	1.4
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	110.1	59.5
0°-40°	149.1	80.6
0°-60°	176.6	95.5
0°-90°	185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	185.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	199	
5°	194	18
15°	156	43
25°	106	49
35°	63	39
45°	25	20
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1248074

CATALOG NUMBER: P3AS02R309027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	199.3
1°	199.3
2°	198.6
3°	197.5
4°	195.9
5°	194.1
6°	191.8
7°	188.9
8°	185.7
9°	182.1
10°	178.4
11°	174.3
12°	170.0
13°	165.5
14°	160.7
15°	155.7
17.5°	143.0
20°	130.3
22.5°	118.0
25°	106.5
27.5°	95.1
30°	84.4
32.5°	73.6
35°	62.7
37.5°	52.0
40°	42.0
42.5°	33.1
45°	25.4
47.5°	18.8
50°	13.2
52.5°	9.3
55°	7.7
57.5°	7.0
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.6
72.5°	3.0
75°	2.5
77.5°	2.0
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.2



TEST NUMBER: P1248074

CATALOG NUMBER: P3AS02R309027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)