

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249454

Luminaire Tested: P3AS13R659027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249454
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 446.0 lumens
Efficiency: N/A
Efficacy: 30.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249454

CATALOG NUMBER: P3AS13R659027DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1249454

CATALOG NUMBER: P3AS13R659027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105189
5°	103918
10°	99976
15°	93644
20°	84241
25°	71520
30°	55933
35°	39859
40°	26077
45°	16126
50°	8187
55°	2906
60°	2544
65°	2542
70°	2308
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16126 cd/sqm

TEST NUMBER: P1249454

CATALOG NUMBER: P3AS13R659027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	9.9
10°-20°	114.8	25.7
20°-30°	134.2	30.1
30°-40°	93.7	21.0
40°-50°	41.3	9.3
50°-60°	9.2	2.1
60°-70°	4.7	1.0
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.3	65.8
0°-40°	387.1	86.8
0°-60°	437.5	98.1
0°-90°	446.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	446.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	480	
5°	472	44
15°	412	115
25°	296	134
35°	149	94
45°	52	41
55°	8	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1249454

CATALOG NUMBER: P3AS13R659027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	479.7
2.5°	477.9
5°	472.1
7.5°	462.3
10°	449.0
12.5°	432.5
15°	412.5
17.5°	388.1
20°	361.0
22.5°	330.3
25°	295.6
27.5°	259.2
30°	220.9
32.5°	184.0
35°	148.9
37.5°	118.2
40°	91.1
42.5°	68.9
45°	52.0
47.5°	38.2
50°	24.0
52.5°	12.4
55°	7.6
57.5°	6.7
60°	5.8
62.5°	5.3
65°	4.9
67.5°	4.0
70°	3.6
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)