

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249459

Luminaire Tested: P3AS13R659027DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659027DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 910.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249459
CATALOG NUMBER: P3AS13R659027DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1249459
 CATALOG NUMBER: P3AS13R659027DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214610
5°	212040
10°	203982
15°	191079
20°	171865
25°	145944
30°	114144
35°	81352
40°	53214
45°	32903
50°	16716
55°	5887
60°	5175
65°	5189
70°	4680
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32903 cd/sqm



TEST NUMBER: P1249459
 CATALOG NUMBER: P3AS13R659027DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	9.9
10°-20°	234.3	25.7
20°-30°	273.8	30.1
30°-40°	191.3	21.0
40°-50°	84.2	9.3
50°-60°	18.7	2.1
60°-70°	9.6	1.1
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.5	65.8
0°-40°	789.8	86.8
0°-60°	892.8	98.1
0°-90°	910.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	979	
5°	963	90
15°	842	234
25°	603	274
35°	304	191
45°	106	84
55°	15	19
65°	10	10
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1249459
CATALOG NUMBER: P3AS13R659027DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	978.7
2.5°	975.0
5°	963.3
7.5°	943.3
10°	916.1
12.5°	882.5
15°	841.7
17.5°	791.8
20°	736.5
22.5°	673.9
25°	603.2
27.5°	528.8
30°	450.8
32.5°	375.5
35°	303.9
37.5°	241.3
40°	185.9
42.5°	140.6
45°	106.1
47.5°	78.0
50°	49.0
52.5°	25.4
55°	15.4
57.5°	13.6
60°	11.8
62.5°	10.9
65°	10.0
67.5°	8.2
70°	7.3
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)