

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249471

Luminaire Tested: P3AS13R659027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 629.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249471

CATALOG NUMBER: P3AS13R659027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1249471

CATALOG NUMBER: P3AS13R659027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159878
5°	155910
10°	145177
15°	130103
20°	112360
25°	93465
30°	73708
35°	54609
40°	37642
45°	23351
50°	12690
55°	7990
60°	6754
65°	6123
70°	5257
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23351 cd/sqm

TEST NUMBER: P1249471

CATALOG NUMBER: P3AS13R659027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.8	10.5
10°-20°	159.3	25.3
20°-30°	176.1	28.0
30°-40°	127.9	20.3
40°-50°	59.9	9.5
50°-60°	20.2	3.2
60°-70°	11.7	1.9
70°-80°	6.1	1.0
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.2	63.8
0°-40°	529.2	84.1
0°-60°	609.3	96.9
0°-90°	629.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	629.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	729	
5°	708	66
15°	573	159
25°	386	176
35°	204	128
45°	75	60
55°	21	20
65°	12	12
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249471

CATALOG NUMBER: P3AS13R659027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	729.1
2.5°	724.6
5°	708.3
7.5°	683.8
10°	652.0
12.5°	614.9
15°	573.1
17.5°	527.8
20°	481.5
22.5°	433.5
25°	386.3
27.5°	338.3
30°	291.1
32.5°	245.8
35°	204.0
37.5°	166.0
40°	131.5
42.5°	100.7
45°	75.3
47.5°	54.4
50°	37.2
52.5°	25.4
55°	20.9
57.5°	18.1
60°	15.4
62.5°	13.6
65°	11.8
67.5°	10.0
70°	8.2
72.5°	7.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)