

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248085

Luminaire Tested: P3AS02R359027DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359027DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 289.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248085

CATALOG NUMBER: P3AS02R359027DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1248085

CATALOG NUMBER: P3AS02R359027DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	103	100		102	100	98		99	98	96		97	95	94
3	107	102	98	95		105	101	97	95		98	96	93		96	94	92		94	92	90
4	104	98	94	91		102	97	93	90		95	92	89		93	90	88		91	89	87
5	100	94	90	87		99	93	89	86		92	88	86		90	87	85		89	86	84
6	97	91	86	83		96	90	86	83		89	85	82		87	84	82		86	83	81
7	94	87	83	80		93	87	83	80		86	82	79		85	81	79		84	81	79
8	91	84	80	77		90	84	80	77		83	79	77		82	79	76		81	78	76
9	89	82	77	74		88	81	77	74		80	77	74		80	76	74		79	76	74
10	86	79	75	72		85	79	75	72		78	74	72		77	74	72		77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188450
5°	184613
10°	171740
15°	125903
20°	64476
25°	23227
30°	9039
35°	3159
40°	1317
45°	341
50°	307
55°	344
60°	307
65°	259
70°	321
75°	424
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 424 cd/sqm

TEST NUMBER: P1248085

CATALOG NUMBER: P3AS02R359027DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	27.1
10°-20°	146.7	50.8
20°-30°	51.9	18.0
30°-40°	9.1	3.1
40°-50°	1.3	0.5
50°-60°	0.7	0.3
60°-70°	0.6	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.8	95.8
0°-40°	285.9	98.9
0°-60°	288.0	99.6
0°-90°	289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	289.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	859	
5°	839	78
15°	555	147
25°	96	52
35°	12	9
45°	1	1
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1248085

CATALOG NUMBER: P3AS02R359027DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	859.4
1°	859.2
2°	856.4
3°	851.2
4°	846.4
5°	838.7
6°	830.7
7°	821.8
8°	810.9
9°	793.8
10°	771.3
11°	740.1
12°	702.6
13°	658.0
14°	608.8
15°	554.6
17.5°	413.1
20°	276.3
22.5°	166.6
25°	96.0
27.5°	57.4
30°	35.7
32.5°	20.7
35°	11.8
37.5°	7.5
40°	4.6
42.5°	2.3
45°	1.1
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1248085
CATALOG NUMBER: P3AS02R359027DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)