

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248091

Luminaire Tested: P3AS02R359027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 116.9 lumens
Efficiency: N/A
Efficacy: 32.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248091

CATALOG NUMBER: P3AS02R359027DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248091

CATALOG NUMBER: P3AS02R359027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77
8	85	77	72	69	84	77	72	69	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59008
5°	56702
10°	49409
15°	37844
20°	25319
25°	15315
30°	8786
35°	4926
40°	2605
45°	1333
50°	648
55°	497
60°	482
65°	415
70°	449
75°	339
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1333 cd/sqm

TEST NUMBER: P1248091

CATALOG NUMBER: P3AS02R359027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.4	20.0
10°-20°	45.4	38.8
20°-30°	29.7	25.4
30°-40°	12.1	10.3
40°-50°	3.6	3.1
50°-60°	1.2	1.0
60°-70°	0.8	0.7
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.6	84.3
0°-40°	110.7	94.6
0°-60°	115.5	98.7
0°-90°	116.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	116.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	269	
5°	258	23
15°	167	45
25°	63	30
35°	18	12
45°	4	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1248091

CATALOG NUMBER: P3AS02R359027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	269.1
1°	268.7
2°	267.4
3°	265.0
4°	262.1
5°	257.6
6°	252.1
7°	245.8
8°	238.8
9°	230.8
10°	221.9
11°	212.0
12°	201.7
13°	190.1
14°	179.1
15°	166.7
17.5°	136.8
20°	108.5
22.5°	83.5
25°	63.3
27.5°	47.2
30°	34.7
32.5°	25.5
35°	18.4
37.5°	13.0
40°	9.1
42.5°	6.3
45°	4.3
47.5°	2.9
50°	1.9
52.5°	1.4
55°	1.3
57.5°	1.2
60°	1.1
62.5°	1.0
65°	0.8
67.5°	0.7
70°	0.7
72.5°	0.6
75°	0.4
77.5°	0.3
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1248091

CATALOG NUMBER: P3AS02R359027DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)