

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249483

Luminaire Tested: P3AS13R709027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 448.0 lumens
Efficiency: N/A
Efficacy: 30.7 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249483

CATALOG NUMBER: P3AS13R709027DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1249483

CATALOG NUMBER: P3AS13R709027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86726
5°	85692
10°	83209
15°	79683
20°	74650
25°	67818
30°	58566
35°	46686
40°	34007
45°	22359
50°	10473
55°	3250
60°	3114
65°	3009
70°	2821
75°	3050
80°	2778
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22359 cd/sqm

TEST NUMBER: P1249483

CATALOG NUMBER: P3AS13R709027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	8.2
10°-20°	98.2	21.9
20°-30°	127.7	28.5
30°-40°	108.3	24.2
40°-50°	55.9	12.5
50°-60°	10.8	2.4
60°-70°	5.8	1.3
70°-80°	3.6	0.8
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	262.6	58.6
0°-40°	370.9	82.8
0°-60°	437.5	97.7
0°-90°	448.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	448.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	396	
5°	389	37
15°	351	98
25°	280	128
35°	174	108
45°	72	56
55°	8	11
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1249483

CATALOG NUMBER: P3AS13R709027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	395.5
2.5°	394.2
5°	389.3
7.5°	382.2
10°	373.7
12.5°	363.0
15°	351.0
17.5°	336.3
20°	319.9
22.5°	301.2
25°	280.3
27.5°	256.7
30°	231.3
32.5°	203.3
35°	174.4
37.5°	145.9
40°	118.8
42.5°	93.4
45°	72.1
47.5°	52.9
50°	30.7
52.5°	13.3
55°	8.5
57.5°	8.0
60°	7.1
62.5°	6.7
65°	5.8
67.5°	5.3
70°	4.4
72.5°	4.0
75°	3.6
77.5°	2.7
80°	2.2
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)