

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248157

Luminaire Tested: P3AS02R459027DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459027DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 197.0 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248157
CATALOG NUMBER: P3AS02R459027DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1248157
 CATALOG NUMBER: P3AS02R459027DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41773
5°	41030
10°	38833
15°	35415
20°	31316
25°	27195
30°	23345
35°	19461
40°	14484
45°	8869
50°	4094
55°	3211
60°	3070
65°	2802
70°	2629
75°	2542
80°	2273
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8869 cd/sqm



TEST NUMBER: P1248157
 CATALOG NUMBER: P3AS02R459027DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	8.8
10°-20°	43.4	22.0
20°-30°	51.6	26.2
30°-40°	44.8	22.8
40°-50°	22.5	11.4
50°-60°	7.8	4.0
60°-70°	5.5	2.8
70°-80°	3.1	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.5	57.1
0°-40°	157.3	79.8
0°-60°	187.5	95.2
0°-90°	197.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	197.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	190	
5°	186	17
15°	156	43
25°	112	52
35°	73	45
45°	29	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1248157
CATALOG NUMBER: P3AS02R459027DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	190.5
2.5°	189.6
5°	186.4
7.5°	181.4
10°	174.4
12.5°	165.7
15°	156.0
17.5°	145.1
20°	134.2
22.5°	123.1
25°	112.4
27.5°	102.2
30°	92.2
32.5°	82.6
35°	72.7
37.5°	62.0
40°	50.6
42.5°	39.5
45°	28.6
47.5°	18.8
50°	12.0
52.5°	9.3
55°	8.4
57.5°	7.7
60°	7.0
62.5°	6.4
65°	5.4
67.5°	4.8
70°	4.1
72.5°	3.4
75°	3.0
77.5°	2.3
80°	1.8
82.5°	1.4
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)