

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248172

Luminaire Tested: P3AS02R509027DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1248172  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R509027DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 316.0 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248172  
CATALOG NUMBER: P3AS02R509027DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1248172  
 CATALOG NUMBER: P3AS02R509027DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68	68	68	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	67	73	69	66	65	65	65	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	110430
5°	107484
10°	102581
15°	92872
20°	80344
25°	65907
30°	37854
35°	11752
40°	3149
45°	1116
50°	273
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1116 cd/sqm



TEST NUMBER: P1248172  
 CATALOG NUMBER: P3AS02R509027DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.7	14.5
10°-20°	113.3	35.9
20°-30°	119.1	37.7
30°-40°	34.1	10.8
40°-50°	3.3	1.1
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.2	88.1
0°-40°	312.3	98.8
0°-60°	315.9	100.0
0°-90°	316.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	316.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	504	
5°	488	46
15°	409	113
25°	272	119
35°	44	34
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1248172  
CATALOG NUMBER: P3AS02R509027DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	503.6
1°	502.8
2°	500.6
3°	497.4
4°	493.0
5°	488.3
6°	483.3
7°	478.0
8°	472.9
9°	467.1
10°	460.7
11°	453.2
12°	444.6
13°	433.9
14°	422.3
15°	409.1
16°	395.0
17°	381.4
18°	367.5
19°	355.2
20°	344.3
21°	333.8
22°	321.9
23°	308.2
24°	292.1
25°	272.4
26°	251.0
27°	227.1
28°	203.4
29°	177.7
30°	149.5
31°	123.1
32°	98.8
32.5°	88.2
33°	77.5
34°	59.4
35°	43.9
36°	32.2
37°	24.0
37.5°	20.7
38°	17.9
39°	13.9
40°	11.0
42.5°	6.2
45°	3.6



TEST NUMBER: P1248172  
CATALOG NUMBER: P3AS02R509027DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	2.0
50°	0.8
52.5°	0.3
55°	0.2
57.5°	0.2
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)