

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248216

Luminaire Tested: P3AS02R559027DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559027DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 193.0 lumens
Efficiency: N/A
Efficacy: 53.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248216

CATALOG NUMBER: P3AS02R559027DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1248216

CATALOG NUMBER: P3AS02R559027DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36291
5°	35835
10°	34402
15°	32191
20°	29356
25°	26203
30°	22915
35°	19033
40°	15000
45°	10172
50°	6209
55°	3211
60°	2982
65°	2854
70°	2629
75°	2288
80°	2273
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10172 cd/sqm

TEST NUMBER: P1248216

CATALOG NUMBER: P3AS02R559027DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.3	7.9
10°-20°	39.6	20.5
20°-30°	49.6	25.7
30°-40°	44.3	22.9
40°-50°	25.9	13.4
50°-60°	8.9	4.6
60°-70°	5.4	2.8
70°-80°	3.0	1.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.5	54.2
0°-40°	148.8	77.1
0°-60°	183.7	95.2
0°-90°	193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	193.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	166	
5°	163	15
15°	142	40
25°	108	50
35°	71	44
45°	33	26
55°	8	9
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1248216

CATALOG NUMBER: P3AS02R559027DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	165.5
2.5°	164.6
5°	162.8
7.5°	159.1
10°	154.5
12.5°	148.9
15°	141.8
17.5°	134.3
20°	125.8
22.5°	117.2
25°	108.3
27.5°	99.4
30°	90.5
32.5°	80.9
35°	71.1
37.5°	61.5
40°	52.4
42.5°	42.6
45°	32.8
47.5°	25.1
50°	18.2
52.5°	11.9
55°	8.4
57.5°	7.5
60°	6.8
62.5°	6.2
65°	5.5
67.5°	4.8
70°	4.1
72.5°	3.4
75°	2.7
77.5°	2.3
80°	1.8
82.5°	1.1
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)