

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248227

Luminaire Tested: P3AS02R609027DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609027DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 294.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248227

CATALOG NUMBER: P3AS02R609027DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1248227

CATALOG NUMBER: P3AS02R609027DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71		
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70214
5°	67422
10°	69404
15°	70307
20°	62072
25°	52309
30°	42437
35°	27626
40°	12681
45°	4869
50°	1637
55°	421
60°	395
65°	363
70°	321
75°	424
80°	253
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4869 cd/sqm

TEST NUMBER: P1248227

CATALOG NUMBER: P3AS02R609027DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	10.0
10°-20°	84.8	28.8
20°-30°	98.9	33.6
30°-40°	63.8	21.7
40°-50°	14.3	4.9
50°-60°	1.4	0.5
60°-70°	0.7	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.2	72.5
0°-40°	277.0	94.2
0°-60°	292.8	99.6
0°-90°	294.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	294.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	320	
5°	306	29
15°	310	85
25°	216	99
35°	103	64
45°	16	14
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1248227

CATALOG NUMBER: P3AS02R609027DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	320.2
2.5°	314.9
5°	306.3
7.5°	305.8
10°	311.7
12.5°	315.6
15°	309.7
17.5°	292.0
20°	266.0
22.5°	239.0
25°	216.2
27.5°	194.0
30°	167.6
32.5°	136.7
35°	103.2
37.5°	70.5
40°	44.3
42.5°	26.6
45°	15.7
47.5°	9.1
50°	4.8
52.5°	1.6
55°	1.1
57.5°	0.9
60°	0.9
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)