

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248247

Luminaire Tested: P3AS02R609027DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1248247  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R609027DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 81.0 lumens  
Efficiency: N/A  
Efficacy: 22.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248247  
CATALOG NUMBER: P3AS02R609027DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1248247  
 CATALOG NUMBER: P3AS02R609027DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	67	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	76	66	60	56	65	60	56	64	59	55	63	59	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20525
5°	20075
10°	18793
15°	16845
20°	14491
25°	11976
30°	9470
35°	7040
40°	4838
45°	3039
50°	1672
55°	994
60°	877
65°	726
70°	641
75°	678
80°	505
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3039 cd/sqm



TEST NUMBER: P1248247  
 CATALOG NUMBER: P3AS02R609027DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	8.5	10.5
10°-20°	20.6	25.5
20°-30°	22.6	27.9
30°-40°	16.5	20.4
40°-50°	7.8	9.6
50°-60°	2.5	3.1
60°-70°	1.4	1.8
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	51.7	63.9
0°-40°	68.2	84.2
0°-60°	78.5	97.0
0°-90°	81.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	81.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	94	
5°	91	8
15°	74	21
25°	50	23
35°	26	16
45°	10	8
55°	3	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1248247  
CATALOG NUMBER: P3AS02R609027DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	93.6
2.5°	93.1
5°	91.2
7.5°	88.3
10°	84.4
12.5°	79.7
15°	74.2
17.5°	68.3
20°	62.1
22.5°	55.8
25°	49.5
27.5°	43.3
30°	37.4
32.5°	31.7
35°	26.3
37.5°	21.4
40°	16.9
42.5°	13.0
45°	9.8
47.5°	7.1
50°	4.9
52.5°	3.2
55°	2.6
57.5°	2.2
60°	2.0
62.5°	1.7
65°	1.4
67.5°	1.2
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)