

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248254

Luminaire Tested: P3AS02R659027DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659027DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248254

CATALOG NUMBER: P3AS02R659027DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1248254

CATALOG NUMBER: P3AS02R659027DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68679
5°	64627
10°	63815
15°	62679
20°	59178
25°	54923
30°	42690
35°	24708
40°	9962
45°	4590
50°	1774
55°	688
60°	614
65°	571
70°	577
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4590 cd/sqm

TEST NUMBER: P1248254

CATALOG NUMBER: P3AS02R659027DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.9	9.9
10°-20°	77.1	27.4
20°-30°	100.9	35.9
30°-40°	58.5	20.8
40°-50°	12.5	4.5
50°-60°	2.0	0.7
60°-70°	1.1	0.4
70°-80°	0.7	0.2
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.9	73.3
0°-40°	264.4	94.1
0°-60°	279.0	99.3
0°-90°	281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	313	
5°	294	28
15°	276	77
25°	227	101
35°	92	58
45°	15	13
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248254

CATALOG NUMBER: P3AS02R659027DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	313.2
2.5°	304.3
5°	293.6
7.5°	289.3
10°	286.6
12.5°	282.7
15°	276.1
17.5°	265.9
20°	253.6
22.5°	242.0
25°	227.0
27.5°	201.8
30°	168.6
32.5°	130.7
35°	92.3
37.5°	58.4
40°	34.8
42.5°	21.8
45°	14.8
47.5°	9.5
50°	5.2
52.5°	2.5
55°	1.8
57.5°	1.6
60°	1.4
62.5°	1.4
65°	1.1
67.5°	0.9
70°	0.9
72.5°	0.7
75°	0.7
77.5°	0.5
80°	0.5
82.5°	0.2
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)