

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248263

Luminaire Tested: P3AS02R659027DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659027DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 271.0 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248263

CATALOG NUMBER: P3AS02R659027DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248263

CATALOG NUMBER: P3AS02R659027DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77		
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63		
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59		
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72626
5°	67422
10°	65196
15°	62838
20°	58105
25°	52939
30°	40892
35°	23718
40°	9418
45°	4000
50°	955
55°	115
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4000 cd/sqm

TEST NUMBER: P1248263

CATALOG NUMBER: P3AS02R659027DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	10.7
10°-20°	77.1	28.5
20°-30°	97.6	36.0
30°-40°	55.6	20.5
40°-50°	11.1	4.1
50°-60°	0.6	0.2
60°-70°	0.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	203.6	75.1
0°-40°	259.2	95.7
0°-60°	270.9	99.9
0°-90°	271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	331	
5°	306	29
15°	277	77
25°	219	98
35°	89	56
45°	13	11
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1248263

CATALOG NUMBER: P3AS02R659027DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	331.2
1°	328.7
2°	323.4
3°	317.1
4°	311.0
5°	306.3
6°	302.9
7°	300.1
8°	297.6
9°	295.2
10°	292.8
11°	290.3
12°	287.6
13°	284.4
14°	280.9
15°	276.8
16°	271.9
17°	266.6
18°	260.8
19°	254.6
20°	249.0
21°	243.2
22°	237.9
23°	232.5
24°	226.1
25°	218.8
26°	210.0
27°	199.4
28°	187.5
29°	174.8
30°	161.5
31°	146.9
32°	132.4
32.5°	125.0
33°	117.7
34°	103.0
35°	88.6
36°	75.2
37°	61.9
37.5°	55.1
38°	49.7
39°	40.2
40°	32.9
42.5°	20.3
45°	12.9

TEST NUMBER: P1248263

CATALOG NUMBER: P3AS02R659027DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.6
50°	2.8
52.5°	0.6
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)