

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248276

Luminaire Tested: P3AS02R659027DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659027DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 77.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248276

CATALOG NUMBER: P3AS02R659027DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248276

CATALOG NUMBER: P3AS02R659027DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19582
5°	19084
10°	17769
15°	15937
20°	13745
25°	11444
30°	9014
35°	6692
40°	4609
45°	2853
50°	1569
55°	994
60°	833
65°	726
70°	641
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2853 cd/sqm

TEST NUMBER: P1248276

CATALOG NUMBER: P3AS02R659027DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.1	10.5
10°-20°	19.5	25.3
20°-30°	21.6	28.0
30°-40°	15.7	20.3
40°-50°	7.3	9.5
50°-60°	2.5	3.2
60°-70°	1.4	1.8
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	49.1	63.8
0°-40°	64.8	84.1
0°-60°	74.6	96.9
0°-90°	77.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	77.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	89	
5°	87	8
15°	70	19
25°	47	22
35°	25	16
45°	9	7
55°	3	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248276

CATALOG NUMBER: P3AS02R659027DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	89.3
2.5°	88.7
5°	86.7
7.5°	83.7
10°	79.8
12.5°	75.3
15°	70.2
17.5°	64.6
20°	58.9
22.5°	53.1
25°	47.3
27.5°	41.4
30°	35.6
32.5°	30.1
35°	25.0
37.5°	20.3
40°	16.1
42.5°	12.3
45°	9.2
47.5°	6.7
50°	4.6
52.5°	3.1
55°	2.6
57.5°	2.2
60°	1.9
62.5°	1.7
65°	1.4
67.5°	1.2
70°	1.0
72.5°	0.9
75°	0.7
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)