

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248334

Luminaire Tested: P3AS05R109027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 254.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248334

CATALOG NUMBER: P3AS05R109027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248334

CATALOG NUMBER: P3AS05R109027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	73		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		68	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109531
5°	101232
10°	80827
15°	61045
20°	46484
25°	35421
30°	25371
35°	16570
40°	10162
45°	6140
50°	4094
55°	3135
60°	2719
65°	2335
70°	2116
75°	2118
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6140 cd/sqm

TEST NUMBER: P1248334

CATALOG NUMBER: P3AS05R109027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.7	16.0
10°-20°	75.2	29.6
20°-30°	66.9	26.3
30°-40°	39.6	15.6
40°-50°	16.3	6.4
50°-60°	7.6	3.0
60°-70°	4.6	1.8
70°-80°	2.4	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	182.8	72.0
0°-40°	222.4	87.6
0°-60°	246.3	97.0
0°-90°	254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	254.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	500	
5°	460	41
15°	269	75
25°	146	67
35°	62	40
45°	20	16
55°	8	8
65°	4	5
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1248334

CATALOG NUMBER: P3AS05R109027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	499.5
1°	498.3
2°	494.5
3°	487.1
4°	474.8
5°	459.9
6°	443.8
7°	424.8
8°	405.0
9°	384.8
10°	363.0
12.5°	313.1
15°	268.9
17.5°	231.0
20°	199.2
22.5°	171.2
25°	146.4
27.5°	122.5
30°	100.2
32.5°	80.0
35°	61.9
37.5°	47.4
40°	35.5
42.5°	26.4
45°	19.8
47.5°	15.3
50°	12.0
52.5°	9.9
55°	8.2
57.5°	7.0
60°	6.2
62.5°	5.4
65°	4.5
67.5°	4.1
70°	3.3
72.5°	2.9
75°	2.5
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)