

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249667

Luminaire Tested: P3AS17R359027DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359027DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 971.9 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249667
CATALOG NUMBER: P3AS17R359027DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1249667
 CATALOG NUMBER: P3AS17R359027DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222044
5°	217323
10°	203537
15°	182703
20°	158914
25°	135419
30°	113435
35°	90346
40°	65322
45°	41338
50°	22549
55°	15598
60°	14736
65°	13698
70°	13079
75°	11184
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 41338 cd/sqm



TEST NUMBER: P1249667
 CATALOG NUMBER: P3AS17R359027DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.9	9.5
10°-20°	223.9	23.0
20°-30°	256.6	26.4
30°-40°	209.4	21.5
40°-50°	105.6	10.9
50°-60°	39.2	4.0
60°-70°	26.3	2.7
70°-80°	14.6	1.5
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.5	58.9
0°-40°	781.9	80.4
0°-60°	926.7	95.3
0°-90°	971.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1013	
5°	987	92
15°	805	224
25°	560	257
35°	338	209
45°	133	106
55°	41	39
65°	26	26
75°	13	15
85°	4	4
90°	0	



TEST NUMBER: P1249667
CATALOG NUMBER: P3AS17R359027DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1012.6
1°	1011.4
2°	1009.0
3°	1004.1
4°	996.9
5°	987.3
6°	975.3
7°	963.3
8°	947.7
9°	932.1
10°	914.1
11°	894.8
12°	874.4
13°	851.6
14°	827.6
15°	804.8
17.5°	743.5
20°	681.0
22.5°	617.4
25°	559.7
27.5°	503.3
30°	448.0
32.5°	392.8
35°	337.5
37.5°	282.3
40°	228.2
42.5°	177.8
45°	133.3
47.5°	96.1
50°	66.1
52.5°	48.0
55°	40.8
57.5°	37.2
60°	33.6
62.5°	30.0
65°	26.4
67.5°	22.8
70°	20.4
72.5°	16.8
75°	13.2
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4



TEST NUMBER: P1249667
CATALOG NUMBER: P3AS17R359027DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)